

Number	K7280/01	Replaces	K7280/93
Issued	2000-07-01	Dated	1993-12-01


Product Certificate

**Copper Tubes**

Based on pre-certification tests as well as periodic inspections by Kiwa, the products referred to in this certificate and marked with the Kiwa-mark as indicated under 'Marking', supplied by

**Buntmetall Amstetten GmbH**

may, on delivery, be relied upon to comply with the Kiwa evaluation guideline BRL-K760 "Copper Tubes".



Bouke Meekma  
Director Kiwa N.V.

This certificate is issued in accordance with the Kiwa-Regulations for Product Certification.

This certificate consists of 2 pages.  
Publication of the certificate is allowed.

\*) This is a translation. Only the Dutch text is legally binding.

Kiwa N.V.  
Sir W. Churchill-laan 273  
P.O. Box 70  
2280 AB RIJSWIJK ZH  
The Netherlands

Phone +31 70 414 44 00  
Fax +31 70 414 44 20  
E-mail [info@kiwa.nl](mailto:info@kiwa.nl)  
[www.kiwa.nl](http://www.kiwa.nl)

**Company**

Buntmetall Amstetten GmbH  
Fabrikstraße 4  
Postfach 43  
A3300 Amstetten  
Tel. +09-43-7472606290  
Fax +09-43-7472606287

Page	2	Number	K7280/01	Replaces	K7280/93
		Issued	2000-07-01	Dated	--

## Copper Tubes

---

### PRODUCT SPECIFICATION

#### General

Copper tubes according guideline BRL-K760 "Copper Tubes" which includes EN 1057 "Copper and copper alloys".

#### Additional specification

Soft copper tubes (R220) in the sizes 10x1,0 mm till 28x 1,2 mm  
Half hard copper tubes (R250) in the sizes 10x1,0 mm till 133x 3,0 mm;

The inside carbon is controlled by the minimum use of liquid oil.

---

### APPLICATION AND USE

The products are meant to be used for domestic distributing networks for hot and cold water.

---

### MARKING

The products are marked with the Kiwa-mark and manufacturers sign.

Place of the mark:

- slightly pressed on each 50 cm on the outside side of the tube.

Obligatory names:

-Hard stamp : SUPERSAN® GASTEC QA KIWA NEN-EN 1057 dia x wall thickness R250/R290 BMA production year/quartile;

Inkt : SUPERSAN® Gastec QA KIWA voor heating and sanitair NEN-EN 1057 dia x wall thickness R250/R290 BMA production year/quartile;

The implementation of the marks is follows:

- indelible (slightly pressed in);
  - Word mark "KIWA"
- 

### RECOMMENDATIONS FOR CUSTOMERS:

1. Check at the time of delivery whether:
    - 1.1 the producer has delivery in accordance with the agreement;
    - 1.2 the mark and the marking method are correct;
    - 1.3 the products show no visible defects as a result of transport etc.
  2. If you should reject a product on the basis of the above, please contact:
    - 2.1 Buntmetall Amstetten GmbH in Amstetten;
    - and, if necessary,
    - 2.2 Kiwa N.V.
  3. Consult the producer's processing guidelines for the proper storage and transport methods.
  4. Check whether this certificate is still valid by consulting [www.kiwa.nl](http://www.kiwa.nl)
-